



Straight 12inch diameter, Integrated Concealment Pole for 5G deployments, to mount and conceal mmWave active antennas, radios and other wireless infrastructure equipment in pole modules.

- Intended to mount and conceal mmWave active antennas and infrastructure equipment utilizing pole modules
- Includes everything needed for a low-power 4G/5G outdoor small cell site
- For 5G radios, integrated AC load center/OVP and Disconnect

Product Classification

Product Type Metro cell site enclosure

Dimensions

Depth 323.9 mm | 12.8 in
Depth Note Round
Height Note 8 ft tall Power Module Base
Pole Diameter 323.9 mm | 12.8 in
Pole Height Options 20.0 ft | 25.0 ft | 30.0 ft | 35.0 ft | 40.0 ft

General Specifications

Color Light Grey (RAL 7035)
Color Notes 760242261AB1HH - Light Grey | 760242261AB2HH - Green | 760242261AB3HH - Black | 760242261AB4HH - Brown | 760242261AB5HH- Beige-Grey | 760242261AB9HH - Metallic Silver | 760242261ABCCH - Faux Concrete | 760242261ABWHH - Pure White
Color Options Beige-Grey (RAL 7006) | Black | Brown (RAL 8014) | Faux Concrete | Green (RAL 6005) | Metallic Silver | Pure White
Finish Aluminum Chromate
Finish Concealment Covers Powder coated
Material Steel

Electrical Specifications

Power/Fiber Input AC load center with OVP and disconnect

Antenna Specifications

Antenna Compatibility, CommScope mmWave active antennas
Antenna Compatibility, Other Vendors mmWave active antennas
Antennas Included None

Radio Specifications

Radio Compatibility, Ericsson	(3) AIR 5121/5331 (Upgradeable to AIR 6701) 760242261E
Radio Compatibility, Nokia	(3) AEUA (Upgradeable to AEWA) 760242261N
Radios Included	None

Environmental Specifications

Cooling	Passive Cooling
Thermal Compliance	GR-487

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant



* Footnotes

Pole Height Options	Overall AGL Standard Height
----------------------------	-----------------------------