



Middle of Pole Micro Concealment Enclosure for up to two high power remote radio heads

- Intended to be used with high powered remote radio heads on standard street lighting and wood pole structures where low-visual impact is desired
- Enables attractive concealment and securing of all site equipment on standard street lighting structures
- Highly-flexible configuration can house diplexers, AC load center, and/or fiber demarcation

## Product Classification

**Product Type** Metro cell site enclosure

## Dimensions

**Depth** 508.0 mm | 20.0 in  
**Height** 1117.6 mm | 44.0 in  
**Weight (loaded)** 136.1 kg | 300.0 lb  
**Weight (unloaded)** 49.9 kg | 110.0 lb  
**Width** 533.4 mm | 21.0 in

## General Specifications

**Color** Light Grey (RAL 7035)  
**Color Notes** SSC-760237600xx1 - Light Grey | SSC-760237600xx2 - Green | SSC-760237600xx3 - Black | SSC-760237600xx4 - Brown  
**Color Options** Black | Brown (RAL 8014) | Green (RAL 6005)  
**Finish Aluminum** Chromate  
**Finish Concealment Covers** Powder coated  
**Material** Aluminum | Steel

## Electrical Specifications

**Power/Fiber Input** Trade size knockouts at rear side

## Antenna Specifications

**Antennas Included** None

## Radio Specifications

**Radio Compatibility, Ericsson** (1) 8843/4449 dual-band high power radio and (2) PSU-AC08 | (2) RRUS11/12/32, 2212, 4415, 4426, 4478 | SSC-760237600E1x

**Radio Compatibility, Nokia** (2) Airscale dual band radios (160W or 320W and (2) Delta 1kW rectifiers (base) | (2) B66A/B25A

# SSC-760237600 | Micro Radio Enclosure

---

4x45W & (2) DC rectifiers | Note: (2) Airscale micro radios can be mounted in place of (1) dual band RRU | SSC-760237600N1x | SSC-760237600N3x

**Radios Included** None

## Mechanical Specifications

**Mounting Options** Wood poles | Tapered poles | Non-tapered poles

## Environmental Specifications

**Cooling** Passive Cooling

**Thermal Compliance** GR-487

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

