



ION® Active Intelligent Point of Interface Subrack with Guide Rails

Product Classification

Brand	ION®
Product Type	Point of interface subrack

General Specifications

Includes	Guide rails
Note	Detailed Product Specifications are available. Please contact your local CommScope representative.
Rack Type	EIA 19 in

Electrical Specifications

Electrical Safety Standard	EN 60950
Power Consumption	276 W
Voltage Range	+10 to +14 Vdc

Supervision And Control

General Alarm	Integrated into management system
----------------------	-----------------------------------

Mechanical Specifications

Interface Slots Available, quantity	1
Mounting	Rack
Slots Available, quantity	8

Environmental Specifications

Operating Temperature	+5 °C to +55 °C (+41 °F to +131 °F)
Relative Humidity	46%–94%
Storage Temperature	-25 °C to +70 °C (-13 °F to +158 °F)

Dimensions

Depth	422.00 mm 16.61 in
--------------	----------------------

Height	177.00 mm 4.00 HE
Width	483.00 mm 19.02 in
Net Weight	7.00 kg 15.43 lb

Packed Dimensions

Depth	600.0 mm 23.6 in
Height	530.0 mm 20.9 in
Width	295.0 mm 11.6 in
Shipping Weight	8.00 kg 17.64 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

