

## imVision Controller Display (Only)

### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	imVision®   iPatch®
<b>Product Type</b>	Controller unit
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### General Specifications

<b>Color</b>	Cool gray
<b>Package Quantity</b>	1

### Dimensions

<b>Height</b>	81.28 mm   3.20 in
<b>Weight</b>	0.25 kg   0.55 lb

### Mechanical Specifications

<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate   Steel
----------------------	---

### Electrical Specifications

<b>Input Voltage</b>	100–240 Vac
----------------------	-------------

### Environmental Specifications

<b>Operating Temperature</b>	0 °C to +50 °C (+32 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Safety Standard</b>	CE   RCM   UL

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

