



## iPatch® M4200i 24 Port UTP Intelligent Universal Modular Panel without Modules

### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	imVision®   iPatch®
<b>Product Type</b>	RJ45 patch panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Dimensions

<b>Depth</b>	25.40 mm   1.00 in
<b>Height</b>	44.45 mm   1.75 in
<b>Weight</b>	0.68 kg   1.50 lb
<b>Width</b>	482.60 mm   19.00 in

### Electrical Specifications

<b>ANSI/TIA Category</b>	6   6A
--------------------------	--------

### Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Safety Standard</b>	ACMA   CE   cUL   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

<b>Intelligence Type</b>	iPatch® enabled
<b>Total Ports, quantity</b>	24
<b>Cable Type</b>	Unshielded
<b>Color</b>	Black
<b>Includes</b>	Cable management bar   Four #12-24 dog point mounting screws   Information outlet removal tool   Instruction sheet   Panel   Two #12 washers   Two #12-24 screws
<b>Package Quantity</b>	1
<b>Rack Units</b>	1.0

### Mechanical Specifications

<b>Panel Style</b>	Straight
<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate

## Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Compliant  
Designed, manufactured and/or distributed under this quality management system

