

## SYSTIMAX 360™ iPatch® G2 1U 32-MPO Distribution Panel, UHD Panel



### Product Classification

|                              |   |
|------------------------------|---|
| <b>Portfolio</b>             | SYSTIMAX®   |
| <b>Brand</b>                 | iPatch®   LazrSPEED®   SYSTIMAX 360™                                |
| <b>Product Type</b>          | Fiber splice panel  |
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |

### Construction Materials

|                      |  |
|----------------------|--|
| <b>Fiber Mode</b>    | Multimode   Singlemode                                     |
| <b>Material Type</b> | Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC) |

### Dimensions

|               |                      |
|---------------|----------------------|
| <b>Depth</b>  | 492.76 mm   19.40 in |
| <b>Height</b> | 44.45 mm   1.75 in   |
| <b>Width</b>  | 482.60 mm   19.00 in |

### Environmental Specifications

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Flammability Rating</b>   | UL 94 V-0                            |
| <b>Operating Temperature</b> | -5 °C to +50 °C (+23 °F to +122 °F)  |
| <b>Relative Humidity</b>     | Up to 95%, non-condensing            |
| <b>Safety Standard</b>       | Austel   CE   CSA   UL               |
| <b>Storage Temperature</b>   | -40 °C to +70 °C (-40 °F to +158 °F) |

### General Specifications

|                              |                 |
|------------------------------|-----------------|
| <b>Intelligence Type</b>     | iPatch® enabled |
| <b>Rack Units</b>            | 1.0             |
| <b>Shelf Movement</b>        | Fixed           |
| <b>Color</b>                 | Black           |
| <b>Interface, front</b>      | MPO             |
| <b>Package Quantity</b>      | 1               |
| <b>Total Ports, quantity</b> | 32              |

### Regulatory Compliance/Certifications

**Agency**

RoHS 2011/65/EU  
ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system

