

## SYSTIMAX 360™ iPatch® G2 2U 96-MPO Distribution Panel, UHD Panel

### Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	iPatch®   LazrSPEED®   SYSTIMAX 360™
<b>Product Type</b>	Fiber splice panel
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

### Construction Materials

<b>Fiber Mode</b>	Multimode   Singlemode
<b>Material Type</b>	Acrylonitrile butadiene styrene (ABS)   Polycarbonate (PC)

### Dimensions

<b>Depth</b>	492.76 mm   19.40 in
<b>Height</b>	88.90 mm   3.50 in
<b>Width</b>	482.60 mm   19.00 in

### Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
<b>Operating Temperature</b>	-5 °C to +50 °C (+23 °F to +122 °F)
<b>Relative Humidity</b>	Up to 95%, non-condensing
<b>Safety Standard</b>	Austel   CE   CSA   UL
<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)

### General Specifications

<b>Intelligence Type</b>	iPatch® enabled
<b>Rack Units</b>	2.0
<b>Shelf Movement</b>	Fixed
<b>Color</b>	Black
<b>Interface, front</b>	MPO
<b>Package Quantity</b>	1
<b>Total Ports, quantity</b>	96

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

