

G2 ULL Multimode OM5 MPO-12 Distribution Module, 2x12F MPO unpinned to 24F LC Lime Green, Method B Enhanced, iPatch Ready



## Product Classification

<b>Portfolio</b>	SYSTIMAX®
<b>Brand</b>	SYSTIMAX ULL
<b>Product Type</b>	Fiber module
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Type</b>	OM5, LazrSPEED® wideband
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Depth</b>	113.28 mm   4.46 in
<b>Height</b>	24.64 mm   0.97 in
<b>Width</b>	95.00 mm   3.74 in

## Environmental Specifications

<b>Qualification Standards</b>	TIA/EIA-568-C.3
<b>Safety Standard</b>	cUL US 1863

## General Specifications

<b>Interface, front</b>	LC
<b>Total Ports, quantity, front</b>	24
<b>Interface Feature, front</b>	Standard
<b>Color, front</b>	Lime green
<b>Adapters, quantity, front</b>	12
<b>Data Module Type</b>	G2
<b>Intelligence Type</b>	iPatch® ready
<b>Shuttered</b>	No
<b>Interface, rear</b>	MPO Unpinned
<b>Adapters, quantity, rear</b>	2
<b>Interface Feature, rear</b>	Key up

**Color, rear** Lime green  
**Package Quantity** 1

## Optical Performance

**Insertion Loss, maximum** 0.35 dB

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

