



Nylon Cable Tie, 14.25 in length

Product Classification

Product Type Cable tie

Dimensions

Nominal Size 1/2 in | 1/4 in | 3/8 in
Compatible Diameter, maximum 16.510 mm | 0.650 in
Compatible Diameter, minimum 10.414 mm | 0.410 in
Height 0.00 mm | 0.00 in
Length 361.95 mm | 14.25 in
Width 4.57 mm | 0.18 in

Environmental Specifications

Operating Temperature -40 °C to +85 °C (-40 °F to +185 °F)

General Specifications

Hanger Type Cable tie
Color Black
Harmonized System (HS) Code 854420 (Coaxial cable and other coaxial electric conductors)
Material Type Engineered plastic
Ordering Note CommScope® standard product in Mexico, Central America, and South America
Package Quantity 50

Mechanical Specifications

Mounting Angle member | Cable ladder | Round member
Tensile Force 222.4 N | 50.0 lbf

Packed Dimensions

Length 37.8 cm | 14.9 in
Shipping Weight 0.35 kg | 0.77 lb
Width 12.2 cm | 4.8 in

Regulatory Compliance/Certifications

Agency **Classification**

40417

RoHS 2011/65/EU
ISO 9001:2015
China RoHS SJ/T 11364-2014

Compliant
Designed, manufactured and/or distributed under this quality management system
Above Maximum Concentration Value (MCV)

