



RJ45 Patch Cord, category 6A, S/FTP Patchcord, 3.0 m, white

OBSOLETE**This product was discontinued on: May 1, 2018****Replaced By**

NPC6ASZDB-WT

NPC RJ45 Patch Cord, category 6A, S/FTP, LSZH, white

Product Classification

Portfolio	NETCONNECT®
Product Type	Twisted pair patch cord
Regional Availability	Asia Australia/New Zealand EMEA

Dimensions

Cord Length	3.00 m 9.84 ft
Diameter Over Jacket	5.59 mm 0.22 in

Electrical Specifications

ANSI/TIA Category	6A
--------------------------	----

Environmental Specifications

Environmental Space	Low Smoke Zero Halogen (LSZH)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)

General Specifications

Cable Type	S/FTP (shielded)
Interface, connector A	RJ45 plug
Interface, connector B	RJ45 plug
Jacket Color	White
Pairs, quantity	4

Mechanical Specifications

Conductor Type	Stranded
-----------------------	----------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

