

SSH-M



SnapStak® Plus Adjustable Hanger for 14mm to 25mm Cable - No Grommets Required. For patents, see www.cs-pat.com.

Product Classification

Brand	SnapStak® Plus
Product Type	Hanger kit

Dimensions

Compatible Diameter, maximum	25.000 mm 0.984 in
Compatible Diameter, minimum	14.000 mm 0.551 in
Height	67.10 mm 2.64 in
Length	48.60 mm 1.91 in
Width	38.00 mm 1.50 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

Environmental Specifications

Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
------------------------------	--------------------------------------

General Specifications

Hanger Type	Snap-in hanger
Accessories	Hangers
Cables per Hanger	1
Color	Silver
Material Type	Stainless steel
Maximum Stack Height	2
Maximum Stack Height, Coaxial	2
Ordering Note	CommScope® standard product in the United States and Canada
Package Quantity	10
Patent Number	US 9,866,004

Mechanical Specifications

Corrosion Resistance, minimum with no degradation	=1000 hours in salt spray chamber
Flammability Test Method	UL 2043
Mounting	3/4 in drilled cable ladder
Vibration Survival	=4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	330.2 mm 13.0 in
Length	260.4 mm 10.3 in
Shipping Weight	0.53 kg 1.17 lb
Width	63.5 mm 2.5 in

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



* Footnotes

Maximum Stack Height Fiber, Hybrid, Power