



Torch Handle Tool Kit with burner heads, safety valve and 4m high pressure hose

- Ideally suited for handling all heat shrink based copper closures
- Progressive regulation, stable flow rate of propane and/or butane
- Flexible connection of gas tube to the handle allows easy handling
- Air regulator to obtain the right flame color ratio (blue/yellow)

Product Classification

Product Type Tool
Regional Availability EMEA | Latin America | North America

General Specifications

Application For use with copper/fiber closures with heat shrink cable ports
Package, quantity 1
Packaging Type Bag | Carton

Dimensions

Height 74.00 mm | 2.91 in
Length 470.00 mm | 18.50 in
Weight 4.80 kg | 10.58 lb
Width 210.00 mm | 8.27 in

Mechanical Specifications

Material Type Aluminum

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



Included Products

299247-000 | FH-1630-PIE-SW4 (Product Component—not orderable) — High Pressure Hose for Torch Tool, 4 meters
295849-000 | FH-1630-S-BN28 (Product Component—not orderable) — Burner Head for Torch Tool, 28 mm nozzle
918209-000 | FH-1630-S-BN38 (Product Component—not orderable) — Burner Head for Torch Tool, 28 mm nozzle

839029-000 | FH-1630-S-HSZ (Product Component—not orderable) — Handgrip Burner handle for Torch Tool

651823-000 | FH-1630-PIE-CV (Product Component—not orderable) — Automatic shut-off Valve for Torch Tool

414431-000 | FH-1630-PIE-R1 (Product Component—not orderable) — Pressure Regulator for Torch Tool