



Torch Handle Tool Kit with piezo-burner heads, safety valve and 4m high pressure hose

- Ideally suited for handling all heat shrink based copper closures
- Progressive regulation, stable flow rate of propane and/or butane
- Flexible connection of gas tube to the handle allows easy handling
- Air regulator to obtain the right flame color ratio (blue/yellow)

Product Classification

Product Type Tool
Regional Availability EMEA | Latin America | North America

General Specifications

Application For use with copper/fiber closures with heat shrink cable ports
Package, quantity 1
Packaging Type Bag | Carton

Dimensions

Height 74.00 mm | 2.91 in
Length 470.00 mm | 18.50 in
Weight 4.80 kg | 10.58 lb
Width 210.00 mm | 8.27 in

Mechanical Specifications

Material Type Aluminum

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant



Included Products

299247-000 | FH-1630-PIE-SW4 (Product Component—not orderable) — High Pressure Hose for Torch Tool, 4 meters
 983099-000 | FH-1630-PIE-BN28 (Product Component—not orderable) — Burner Head for Torch Tool, 28 mm nozzle
 201385-000 | FH-1630-PIE-BN38 (Product Component—not orderable) — Burner Head for Torch Tool, 38 mm nozzle

354957-000 | FH-1630-PIE-BN50 (Product Component—not orderable) — Burner Head for Torch Tool, 50 mm nozzle

149567-000 | FH-1630-PIE-LGS (Product Component—not orderable) — Safety Regulator for Torch Tool

660983-000 | FH-1630-PIE (Product Component—not orderable) — Handgrip Burner handle, piezo-electric for Torch Tool