



CWST wraparound repair sleeve heat shrink kit, unpressurized, for 12 to 55 mm cable diameter, 750 mm long

- Excellent split resistance of the composite structure offers superior resistance to mechanical abuse during and after the installation
- Integrated moisture barrier completely reconstitutes the cable sheath construction

Product Classification

Product Series	CWST
Product Type	Heat shrink repair sleeve
Regional Availability	EMEA

Dimensions

Length	750.00 mm 29.53 in
---------------	----------------------

Environmental Specifications

Environmental Space	Aerial Buried Ducted
----------------------------	--------------------------

General Specifications

Color	Black
Expanded Wall Thickness, minimum	1.10 mm 0.04 in
Material Type	Fiber-reinforced multi-layer sealing sleeve
Package Quantity	1
Packaging Type	Bag Carton
Sealant Type	Hotmelt adhesive
Single Cable Diameter, maximum	55.00 mm 2.17 in
Single Cable Diameter, minimum	12.00 mm 0.47 in

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

