



MWTM Medium-Wall Heat-Shrinkable Tubing kit, 115 mm/34 mm Shrink ratio, 1000 mm long, uncoated, 5 pcs

- Flexible in use and installation due to its high shrink ratio
- Hotmelt adhesive version used where high mechanical and sealing performance is required
- Uncoated version used as an electrical insulator

Product Classification

Product Series	MWTM
Product Type	Heat shrink tubing, medium wall
Regional Availability	EMEA

Dimensions

Length 1000.00 mm | 39.37 in

Environmental Specifications

Environmental Space Aerial | Ducted

General Specifications

Color	Black
Expanded Inside Diameter, minimum	115.00 mm 4.53 in
Material Type	Polyolefin
Package Quantity	5
Packaging Type	Bag Carton
Recovered Inside Diameter, maximum	34.00 mm 1.34 in
Recovered Wall Thickness, minimum	2.00 mm 0.08 in
Sealant Type	Uncoated

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

