



MWTM Medium-Wall Heat-Shrinkable Tubing kit, 25 mm/8 mm Shrink ratio, 1000 mm long, uncoated, 10 pcs

- Flexible in use and installation due to its high shrink ratio
- Hotmelt adhesive version used where high mechanical and sealing performance is required
- Uncoated version used as an electrical insulator

## Product Classification

<b>Product Series</b>	MWTM
<b>Product Type</b>	Heat shrink tubing, medium wall
<b>Regional Availability</b>	EMEA

## Dimensions

<b>Length</b>	1000.00 mm   39.37 in
---------------	-----------------------

## Environmental Specifications

<b>Environmental Space</b>	Aerial   Ducted
----------------------------	-----------------

## General Specifications

<b>Color</b>	Black
<b>Expanded Inside Diameter, minimum</b>	25.00 mm   0.98 in
<b>Material Type</b>	Polyolefin
<b>Package Quantity</b>	10
<b>Packaging Type</b>	Bag   Carton
<b>Recovered Inside Diameter, maximum</b>	8.00 mm   0.31 in
<b>Recovered Wall Thickness, minimum</b>	2.00 mm   0.08 in
<b>Sealant Type</b>	Uncoated

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

