



MWTM Medium-Wall Heat-Shrinkable Tubing kit, 35 mm/12 mm Shrink ratio, 1000 mm long, uncoated, 10 pcs

- Flexible in use and installation due to its high shrink ratio
- Hotmelt adhesive version used where high mechanical and sealing performance is required
- Uncoated version used as an electrical insulator

## Product Classification

<b>Product Series</b>	MWTM
<b>Product Type</b>	Heat shrink tubing, medium wall
<b>Regional Availability</b>	EMEA

## Dimensions

**Length** 1000.00 mm | 39.37 in

## Environmental Specifications

**Environmental Space** Aerial | Ducted

## General Specifications

<b>Color</b>	Black
<b>Expanded Inside Diameter, minimum</b>	35.00 mm   1.38 in
<b>Material Type</b>	Polyolefin
<b>Package Quantity</b>	10
<b>Packaging Type</b>	Bag   Carton
<b>Recovered Inside Diameter, maximum</b>	12.00 mm   0.47 in
<b>Recovered Wall Thickness, minimum</b>	2.00 mm   0.08 in
<b>Sealant Type</b>	Uncoated

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant

