

243095-38



Stainless Steel Hardware Kit for 1-1/4 in or 1-5/8 in Block style hangers (4 stack), includes 3/8 in bolts and hardware, 305 mm (11.87 in) length

Product Classification

Product Type	Hardware kit
Product Brand	HELIAX®
Ordering Note	CommScope® standard product (Global)

General Specifications

Thread Size 3/8 in

Dimensions

Maximum Stack Height	4
Length	301.498 mm 11.87 in
Nominal Size	1-1/4 in 1-5/8 in

Material Specifications

Material Type Stainless steel 304

Packaging and Weights

Height, packed	254 mm 10 in
Width, packed	88.9 mm 3.5 in
Length, packed	330.2 mm 13 in
Included	Forty flat washers Forty lock washers Ten 3/8 in threaded rods Twenty hex nuts
Packaging quantity	10
Weight, gross	1.361 kg 3 lb

* Footnotes

Maximum Stack Height Fiber, Hybrid, Power