

252137



Six 4" Port Entrance Panel, 2 x 3

Product Classification

Product Type	Entrance panel
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Color	Gray
Entry Panel Port Size	101.6 mm 4 in
Number of Ports	6
Panel Type	Multiple

Dimensions

Height	444.5 mm 17.5 in
Width	584.2 mm 23 in

Material Specifications

Material Type	Aluminum
----------------------	----------

Environmental Specifications

Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

Packaging and Weights

Height, packed	203.2 mm 8 in
Width, packed	254 mm 10 in
Length, packed	254 mm 10 in
Included	Entry cap Hardware Port
Packaging quantity	1
Weight, gross	1.75 kg 3.858 lb

Regulatory Compliance/Certifications

Agency	Classification
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Included Products

CAP-4 – Snap-in Entry Port Cap, 4 in

CAP-4



Snap-in Entry Port Cap, 4 in

Product Classification

Product Type	Port cap
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Color	Black
Entry Panel Port Size	4 in 101.6 mm
Panel Type	Multiple

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Packaging and Weights

Height, packed	5 in 127 mm
Width, packed	5 in 127 mm
Length, packed	9.8 in 248.92 mm
Included	Entry cap
Packaging quantity	1
Weight, gross	0.02 kg 0.044 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

