


252139



Twelve 4" Port Entrance Panel, 3 x 4

Product Classification

Product Type	Entrance panel
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Color	Gray
Entry Panel Port Size	101.6 mm 4 in
Number of Ports	12
Panel Type	Multiple

Dimensions

Height	647.7 mm 25.5 in
Width	647.7 mm 25.5 in

Material Specifications

Material Type	Aluminum
----------------------	----------

Environmental Specifications

Weather Resistance Test Method	04AS00-03.9.0 IEC 60529:2001, IP66
---------------------------------------	--------------------------------------

Packaging and Weights

Height, packed	698.5 mm 27.5 in
Width, packed	698.5 mm 27.5 in
Length, packed	1,778 mm 70 in

252139

Included	Entry cap Hardware Port
Packaging quantity	1
Weight, gross	3.62 kg 7.981 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CAP-4 – Snap-in Entry Port Cap, 4 in

CAP-4



Snap-in Entry Port Cap, 4 in

Product Classification

Product Type	Port cap
Product Brand	HELIAX®
Ordering Note	CommScope® non-standard product

General Specifications

Color	Black
Entry Panel Port Size	101.6 mm 4 in
Panel Type	Multiple

Material Specifications

Material Type	Engineered plastic
----------------------	--------------------

Packaging and Weights

Height, packed	127 mm 5 in
Width, packed	127 mm 5 in
Length, packed	248.92 mm 9.8 in
Included	Entry cap
Packaging quantity	1
Weight, gross	0.02 kg 0.044 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant
UK-ROHS	Compliant

