

760258663 | FMS-K1BI-L1A1-24-SP-EU



FMS Fiber Optic Panel, 1U, 19 in, black, Includes 12 x LC SM Duplex Adaptors (24F), 24 x SM LC Pigtails. 24 x Splice protectors. Splice tray and cable glands

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FMS

General Specifications

Functionality	Patching Splicing
Body Style	Symmetrical
Cable Exit Location	Rear, left side
Color	Black
Interface, front	LC/UPC
Fiber Color Code	TIA-598
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Splice Trays Included, quantity	1
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	24

Dimensions

Height	44.3 mm 1.744 in
Width	482.2 mm 18.984 in
Depth	344.2 mm 13.551 in

Material Specifications

Finish	Powder coated
---------------	---------------

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A1

Insertion Loss, maximum 0.3 dB

Return Loss, minimum 45 dB

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

