

760258675 | FMS-K1BA-L5M4-12-SP-DIN



FMS Fiber Optic Panel, 1U, 19 in, black, Includes 6 x LC OM4 Duplex Adaptors (12F), 12 x MM LC Pigtails. 12 x Splice protectors. Splice tray and cable glands

Product Classification

Regional Availability	DACH countries
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	FMS
Ordering Note	Specific panel MID according to local requirements in DACH region

General Specifications

Functionality	Patching Splicing
Body Style	Symmetrical
Cable Exit Location	Rear, left side
Color	Black
Interface, front	LC/UPC
Fiber Color Code	DIN VDE 0888
Rack Type	EIA 19 in
Rack Units	1
Shelf Movement	Sliding
Splice Trays Included, quantity	1
Splicing Type	Heat shrink, single fiber fusion
Total Ports, quantity	12

Dimensions

Height	44.3 mm 1.744 in
Width	482.2 mm 18.984 in
Depth	344.2 mm 13.551 in

Material Specifications

Finish	Powder coated
---------------	---------------

760258675 | FMS-K1BA-L5M4-12-SP-DIN

Material Type Steel

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4

Insertion Loss, maximum 0.3 dB

Return Loss, minimum 27 dB

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

