SFG22HDX-15-4-H10



G22HDX Tower Sector Frame with extended face, 15 ft x 2.88 in OD face pipes. Base Kit Only. Includes four 2.88 OD x 120 in antenna pipes

Product Classification

Product Type High capacity Tower sector frame

Product Brand PIM-guard

Product Series G2

General Specifications

Mounting Angle 60°, 203.2 mm (8 in) | Straight or tapered legs up to 203.2 mm (8 in) OD

Pipe, quantity 4
Sectors, quantity 1

Tower Taper Non-tapered | Tapered

Dimensions

Face Width 4.572 m | 15 ft

Width 4,572 mm | 180 in

Face Support Pipe Diameter 73.025 mm | 2.875 in

Mounting Diameter, maximum 218.44 mm | 8.6 in

Mounting Diameter, minimum 38.1 mm | 1.5 in

Pipe Outer Diameter 73.025 mm | 2.875 in

Stand-off Distance 1,066.8 mm | 42 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Frame | Plain end pipes (4) | Stiff arms (2) | Tower attachment

ANDREW® an Amphenol company

SFG22HDX-15-4-H10

Packaging quantity 1

Weight, net 371.039 kg | 818 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



* Footnotes

Wind Rating BWS—Base Wind Speed; FBC—Florida Building Code

