

FE-182308-F12



HELIAX® Fiber Junction Box for 1 Trunk / 6 Jumper Cables

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Outdoor junction box
Product Brand	HELIAX®

General Specifications

Application	Used as a fiber/power junction box
Cable Entry, quantity, maximum, bottom	7
Color	Black
Fiber System Configuration Type	Hybrid with OVP, 6 RRU
Mounting	Pipe, 44–114 mm (1.75–4.5 in) OD Wall

Dimensions

Height	233.985 mm 9.212 in
Width	181.991 mm 7.165 in
Depth	85.979 mm 3.385 in
Cable Entry Fiber Gland Size, maximum	5 mm 0.197 in
Cable Entry Fiber Gland Size, minimum	5 mm 0.197 in
Cable Entry Jumper Gland Size, maximum	5 mm 0.197 in
Cable Entry Jumper Gland Size, minimum	5 mm 0.197 in

Material Specifications

Material Type	High-impact polycarbonate, UV resistant
----------------------	---

Environmental Specifications

Operating Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
------------------------------	--------------------------------------

FE-182308-F12

Environmental Space	Indoor Outdoor
Qualification Standards	IEC 60529:2001, IP67
Packaging and Weights	
Included	Mounting kit
Weight, net	1.5 kg 3.307 lb