

F090CCB1



FlexTwist® Flexible Twist for WR90, 10.7–11.7 GHz, with interface types CPR90G and CPR90G, 300 mm

Product Classification

| | |
|----------------------|---------------------------------------|
| Product Type | Rectangular waveguide, flexible twist |
| Product Brand | FlexTwist® |

General Specifications

| | |
|--------------------|----------------|
| Component | Flexible Twist |
| Interface | CPR90G |
| Interface 2 | CPR90G |

Dimensions

| | |
|-----------------------|--------------------|
| Length | 300 mm 11.811 in |
| Waveguide Size | WR90 WG16 R100 |

Electrical Specifications

| | |
|---------------------------------|-------------------------|
| Attenuation | 0.43 dB/m 0.131 dB/ft |
| Average Power | 960 W |
| Operating Frequency Band | 10.7 – 11.7 GHz |
| Peak Power | 180 kW |
| VSWR | 1.05 |

Mechanical Specifications

| | |
|--|---------------------------------|
| Minimum Bend Radius, Multiple Bends (E Plane) | 64 mm 2.52 in |
| Minimum Bend Radius, Multiple Bends (H Plane) | 127 mm 5 in |
| Maximum Twist | 310 °/m 94.488 °/ft |
| Pressurization, maximum | 0.31 N/mm ² 45 psi |

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

