


# CX3760001 | 200T040QR860JCASS COEX

ConQuest® Cable in Conduit, 2 in, SCH 40, terracotta, QR 860 JCASS



## Product Classification

Product Type	Coaxial cable-in-conduit
Product Brand	ConQuest®
Product Series	860 Series

## General Specifications

Cable Type	860 series
Cable-In-Conduit Type	QR® in duct
Color	Terracotta
Conduit Type	Non-toneable
Wall Type	Smooth

## Dimensions

Length	822.96 m   2700 ft
Wall Thickness Designation	SCH 40
Nominal Size	2 in

## Packaging and Weights

Weight, net	1,022.369 kg/km   687 lb/kft
-------------	------------------------------

## Included Products

5543802 QR® 860 JCASS	–	75 Ohm QR® Trunk and Distribution Cable, black PE jacket, flooded for underground
CX3799999 200T040 EMPTY DUCT COEX	–	ConQuest® Empty Conduit, 2 in, SCH 40, terracotta