



IFDB Fiber Optic Wall Box, plug & play, with 1 SC/UPC adapter port and pigtail

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	IFDB

## General Specifications

<b>Functionality</b>	Patching   Splitting
<b>Adapters, quantity</b>	4
<b>Color</b>	Light gray
<b>Front Cover Type</b>	Screw-on
<b>Interface</b>	SC/UPC
<b>Mounting</b>	Floor   Wall

## Dimensions

<b>Height</b>	125 mm   4.921 in
<b>Width</b>	125 mm   4.921 in
<b>Depth</b>	55 mm   2.165 in

## Material Specifications

<b>Material Type</b>	Thermoplastic
----------------------	---------------

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

# 760234769 | IFDB-PNP-S1

---

<b>Environmental Space</b>	Indoor
<b>Flammability Rating</b>	UL 94 V-0
<b>Qualification Standards</b>	IEC 60529, IP30

## Packaging and Weights

<b>Included</b>	Fiber pigtail assemblies
<b>Packaging quantity</b>	12
<b>Packaging Type</b>	Bag   Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

