


760243590 | PNL-BK-024-KHB-LC02-RO-NS



Adapter Pack, Black, 1000-Type, with 12 duplex keyed hybrid LC adapters, rose, no shutter

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter pack
Product Series	1000-style

General Specifications

Application	Used in conjunction with SD Panels Used in conjunction with panels and enclosures (rack, wall, and floor mount) that accept 1000 style panels
Adapter Color	Rose
Adapter Cutout, quantity	12
Adapters, quantity	12
Body Style	Duplex
Interface	LC/UPC
Interface Feature	Keyed Hybrid
Pigtails Included, quantity	0
Shuttered	No
Total Ports, quantity	24

Optical Specifications

Fiber Mode	Multimode Singlemode
-------------------	------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

UK-ROHS

Compliant/Exempted

