



CHD 12 port LC field term splice cassette

Product Classification

Product Type	Fiber cassette
Product Series	CHD

General Specifications

Adapters, quantity, front	12
Interface, front	Unloaded
Total Fibers, quantity	12
Total Ports, quantity, front	12

Dimensions

Height	12.446 mm 0.49 in
Width	83.82 mm 3.3 in
Depth	184.658 mm 7.27 in

Environmental Specifications

Safety Standard	cUL US 1863
------------------------	-------------

Packaging and Weights

Packaging quantity	1
Weight, net	0.454 kg 1 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value

760244827 | CHD-FT-00-LC-00

ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
RCM	Compliant to electrical safety & telecommunications requirements
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

