CR9106-000 | FTUO-M-U-NN-1



FTUO Fiber Termination Unit Outdoor Wall Box with universal splice holder for 8 splices

- Typically used as a transition point where the OSP cable is spliced to an indoor cable
- Allows the installation of fibers with a minimum bend radius of 25 mm over a length of 2m
- In-line and single-ended enclosure coonfiguration possible for main cable
- Cable inlet is provided at the bottom left side. Optionally the main cable can continue at the top left side.
- Universal splice holder can hold SMOUV and ANT splice protector types

Product Classification

Regional Availability EMEA

Product Type Fiber wall box

Product Series FTUO
Minimum Order Quantity 10

General Specifications

Functionality Splicing **Access** Front

Application For drop cables up to 5 mm diameter | For main cables up to 12 mm diameter

Cable Entry Location Back | Bottom left | Bottom right | Top left | Top right

Cable Ports, quantity 5

Enclosure Color Gray

InterfaceSplicing onlyLock TypeLocking screw

Mounting Wall

Splicing Capacity, maximum 8

Dimensions

 Height
 168 mm | 6.614 in

 Width
 132 mm | 5.197 in

 Depth
 33 mm | 1.299 in

Material Specifications



CR9106-000 | FTUO-M-U-NN-1

Enclosure Material Type Polycarbonate + ASA

Environmental Specifications

Environmental Space Outdoor
Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP40 when cable enters from top | IEC 60529, IP43 when cable enters from bottom

UV Resistance UV stabilized

Packaging and Weights

Included Hook and loop fastener | Rubber seal | Silicone tube | Splice protector holder | Tie wraps

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

