

# FMT-GTL080A20-A48P

---

FMT Fiber Termination/Splice Panel, with sliding tray, 48 LC/UPC, singlemode, 2RU, 19 in, putty white



## Product Classification

<b>Regional Availability</b>	Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber patch/splice panel
<b>Product Series</b>	FMT

## General Specifications


<b>Functionality</b>	Patching   Splicing
<b>Body Style</b>	Symmetrical
<b>Color</b>	Black
<b>Color, front</b>	Putty white
<b>Interface, front</b>	LC
<b>Interface Feature, front</b>	Standard
<b>Rack Type</b>	EIA 19 in   EIA 23 in
<b>Rack Units</b>	2
<b>Shelf Movement</b>	Sliding
<b>Total Ports, quantity</b>	48

## Dimensions

<b>Height</b>	88.9 mm   3.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	279.91 mm   11.02 in

## Ordering Tree

# FMT-GTL080A20-A48P



## Material Specifications

**Finish** Powder coated

**Material Type** Steel

## Optical Specifications

**Fiber Mode** Singlemode

## Packaging and Weights

**Included** Mounting hardware

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

