



FDH 3000 Plug-and-Play CWDM Module, 8-channel, SC/APC

- Rugged packaging is built for high performance, while the Plug-and-Play design reduces installation time
- Bend-optimized fiber and ruggedized extreme temperature cabling
- Easy to insert and remove without affecting adjacent splitters
- Reversible dust cap makes test and turn-up easy

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	FDH 3000 Mini FDH 3000

General Specifications

Device Type	Plug-and-play module
Functionality	Demultiplexing
Application	For use in FDH 3000 cabinets
Circuits, quantity	1
Distribution Type	8-channel CWDM
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Multiplexers, quantity	1

Dimensions

Height	88.9 mm 3.5 in
Width	12.7 mm 0.5 in
Depth	139.7 mm 5.5 in

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
-----------------------	--------------------------------------

FPS-C1JJ108CA2AD1 | 300100116582

Flammability Rating	UL 94 V-0
Qualification Standards	Telcordia GR-1209-CORE Telcordia GR-1221-CORE Telcordia GR-326-CORE

Packaging and Weights

Included	Reversible dust cap
Packaging quantity	1
Packaging Type	Bag Carton