

# FPS-C1JJBE0CN1000



## FDH 3000 Plug-and-Play CWDM Module, 4-channel, SC/APC

- Rugged packaging is built for high performance, while the Plug-and-Play design reduces installation time
- Bend-optimized fiber and ruggedized extreme temperature cabling
- Easy to insert and remove without affecting adjacent splitters
- Reversible dust cap makes test and turn-up easy

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	CWDM module
Product Series	FDH 3000   Mini FDH 3000

## General Specifications

Device Type	Plug-and-play module
Functionality	Demultiplexing   Multiplexing
Access	Front   Rear
Application	For use in FDH 3000 cabinets
Circuits, quantity	1
Distribution Type	4-channel CWDM
Interface, front	SC/APC
Interface, Input	SC/APC
Interface, Output	SC/APC
Interface, rear	SC/APC
Module Color	Putty white
Multiplexers, quantity	1

## Dimensions

Height	88.9 mm   3.5 in
Width	12.7 mm   0.5 in
Depth	139.7 mm   5.5 in

# FPS-C1JJBE0CN1000

## Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Flammability Rating	UL 94 V-0
Qualification Standards	Telcordia GR-1209-CORE   Telcordia GR-1221-CORE   Telcordia GR-326-CORE

## Packaging and Weights

Included	Reversible dust cap
Packaging quantity	1
Packaging Type	Bag   Carton

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

