

FPS-WP04W055NN0



FDH 3000 Plug-and-Play Splitter Module, quad, 1 x 2, SC/UPC

- Rugged packaging is built for high performance, while the Plug-and-Play design reduces installation time
- Bend-optimized fiber and ruggedized extreme temperature cabling
- Easy to insert and remove without affecting adjacent splitters
- Reversible dust cap makes test and turn-up easy

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Splitter module
Product Series	FDH 3000 Mini FDH 3000

General Specifications

Device Type	Plug-and-play module
Functionality	Splitting
Access	Front Rear
Application	For use in FDH 3000 cabinets
Circuits, quantity	4
Distribution Type	1 x 2 splitter (4)
Interface, front	SC/UPC
Interface, Input	SC/UPC
Interface, Output	SC/UPC
Interface, rear	SC/UPC
Module Color	Putty white
Split Ratio	Symmetrical
Splitter, quantity	4

Dimensions

Height	88.9 mm 3.5 in
Width	12.7 mm 0.5 in
Depth	139.7 mm 5.5 in

FPS-WP04W055NN0

Environmental Specifications

Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Flammability Rating	UL 94 V-0
Qualification Standards	Telcordia GR-1209-CORE Telcordia GR-1221-CORE Telcordia GR-326-CORE

Packaging and Weights

Included	Reversible dust cap
Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

