171586-000 | FIST-GPS2-I-IAB-6

FIST-GPS2 Fiber Termination/Splice Panel, 3RU, with 6 trays, 19 in, gray

Product Classification

Regional Availability EMEA

Portfolio CommScope®

Product Type Fiber patch/splice panel

Product Brand FIST®

Product Series FIST-GPS2

General Specifications

Functionality Patching | Splicing

Application Used in FIST-GR3-style frames only

ColorGrayColor, frontGray

Interface, front Unloaded

Rack Type EIA 19 in | ETSI 600 mm

Rack Units 3

Shelf Movement Sliding

Dimensions

 Height
 133.35 mm | 5.25 in

 Width
 482.6 mm | 19 in

Material Specifications

Finish Powder coated

Material Type Galvanized steel

Environmental Specifications

Operating Temperature $-5 \,^{\circ}\text{C}$ to $+45 \,^{\circ}\text{C}$ ($+23 \,^{\circ}\text{F}$ to $+113 \,^{\circ}\text{F}$)

Storage Temperature -30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity Up to 93%, non-condensing

Packaging and Weights



171586-000 | FIST-GPS2-I-IAB-6

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

