

FDC-L17USX20101020



FDC Fiber Optic Wall Box, 12-position, Singlemode SC

Product Classification

Regional Availability	North America
Product Type	Fiber wall box
Product Series	FDC

General Specifications

Functionality	Patching Splicing
Access	Front
Application	Accepts LGX-style Value Added Modules
Cable Type	Pigtails - Stranded
Enclosure Color	Putty white
Interface	SC/UPC
Mounting	Wall
Port, quantity	12

Dimensions

Height	307 mm 12.087 in
Width	470 mm 18.504 in
Depth	177.04 mm 6.97 in

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Outdoor
Qualification Standards	NEMA, Type 4

Packaging and Weights

FDC-L17USX20101020

Included	Compression fitting Tie-off adapter
Packaging quantity	1
Packaging Type	Box Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

