


# FDT-GN224NXB0000

---



OFDT Outdoor Fiber Distribution Terminal, 24-fiber, SC/UPC, 2 splice trays, with pigtails

- OFDT is a compact and secure family of enclosures by connecting fiber cables at MDUs
- Features a unique “swing frame” type design that separates the splicing in the rear from the patch access in the front
- Accommodates a variety of OSP cable types via sealed grommet entry with standard grip clamps
- Robust steel construction protects fibers against damage and ensures network reliability

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber distribution terminal
<b>Product Series</b>	OFDT

## General Specifications

<b>Functionality</b>	Patching   Splicing
<b>Access</b>	Front
<b>Cable Type</b>	Pigtails - Stranded
<b>Enclosure Color</b>	Putty white
<b>Front Door Type</b>	Double hinged
<b>Interface</b>	SC/UPC
<b>Lock Type</b>	Padlock ready
<b>Mounting</b>	Wall
<b>Port Capacity, maximum</b>	24
<b>Port, quantity</b>	24

## Dimensions

<b>Height</b>	342.9 mm   13.5 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	203.2 mm   8 in

## Material Specifications

<b>Enclosure Material Type</b>	Steel
<b>Finish</b>	Powder coated

# FDT-GN224NXB0000

---

## Optical Specifications

**Fiber Mode** Singlemode

## Environmental Specifications

**Environmental Space** Outdoor

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

