

Fiber Optic Module, 12 LC ports at front, 2 MPO at rear, OM3 fiber, angle right

OBSOLETE

Product Classification

| | |
|------------------------------|--|
| Regional Availability | Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber module |

General Specifications

| | |
|----------------------------------|-------------------------------|
| Functionality | Breakout |
| Adapter Color | Blue |
| Adapters, quantity, front | 6 |
| Body Style | Duplex Straight orientation |
| Color, front | Black |
| Color, housing | Black |
| Color, rear | Black |
| Input Ports, quantity | 12 |
| Interface, front | LC/UPC |
| Interface, rear | MPO |
| Interface Feature, rear | Standard |
| Polarity | Pairs, flipped |

Dimensions

| | |
|---------------|--------------------|
| Height | 28.96 mm 1.14 in |
| Width | 129.54 mm 5.1 in |
| Depth | 114.3 mm 4.5 in |

Optical Specifications

| | |
|-------------------|-----------|
| Fiber Mode | Multimode |
| Fiber Type | OM3 |

Packaging and Weights

| | |
|---------------------------|--------------|
| Packaging quantity | 1 |
| Packaging Type | Bag Carton |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

