



Highband® 12-module Kit, category 6A, 20-pair modules

Product Classification

Regional Availability	Australia/New Zealand
Product Type	Back mount frame kit
Product Brand	Highband®
Product Series	Highband

General Specifications

ANSI/TIA Category	6A
Modules, quantity	12
Mounting	Backmount frames
Pairs, quantity	240
Termination Punchdowns, minimum	200 times
Termination Tool	LSA-PLUS Punchdown tool
Termination Type	IDC
Transmission Standards	IEEE 802.3an TIA/EIA-568 Cat 6A

Dimensions

Compatible Conductor Gauge, solid	26–22 AWG
Compatible Conductor Gauge, stranded	26–22 AWG

Electrical Specifications

Current Rating, maximum	2.5 A
Insulation Resistance, minimum	50 MΩ
Safety Voltage Rating	150 Vac

Material Specifications

Contact Plating Material	Silver
---------------------------------	--------

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Environmental Specifications

Environmental Space Indoor | Outdoor

Flammability Rating UL 94 V-0

Safety Standard UL 1863

Packaging and Weights

Included Label holder | Rear cable management

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

