NG4-MMDCMOROOO



NG4access® MPO Module, multimode, LC/UPC-MPO 24 fiber, right exit (for MPO module)

- Offers the same craft-friendly interface for LC and SC connectors as the cabled module
- Allow installers to connect an MPO trunk cable to turn up services in rapid installation applications

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	NG4access®
Product Series	NG4

General Specifications

Functionality	Breakout
Application	NG4 MPO module
Adapter Color	Aqua
Adapters, quantity, front	12
Body Style	Duplex
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	MPO
Polarity	Method A
Total Fibers, quantity	12
Total Ports, quantity, front	24
Dimensions	
Height	13.21 mm 0.52 in

5		
Width	159.77 mm 6.	.29 in
Depth	122.68 mm 4.	.83 in

Page 1 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023



NG4-MMDCMOROOO

Outline Drawing



Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM4, bend insensitive

Environmental Specifications

Operating Temperature	-5 °C to +40 °C (+23 °F to +104 °F)
Storage Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Relative Humidity	Up to 85%, non-condensing

Packaging and Weights

Packaging quantity	1	
Packaging Type	Bag	Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted

Page 2 of 3

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023



NG4-MMDCMOROOO



Compliant



©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 10, 2023

