NG4-VMKLF4J



NG4access® Module VAM, Monitoring, 60/40, singlemode, LC/UPC, front, left, 4 circuits

- VAMs help enhance optical transport systems by providing flexible, easy to incorporate optical components into the network
- VAMs increase fiber capacity and help troubleshooting or distributing signals to multiple subscribers
- *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Monitoring module

Product Brand NG4access®

Product Series NG4

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

Device Type Plug-and-play module

Functionality Monitoring

Access Front

Application For use with NG4 access frames

Circuits, quantity 4

Distribution Type 1 x 2 splitter

Interface, front LC/UPC
Interface, Input LC/UPC
Interface, Output LC/UPC

Location of Manufacturing Waived per BABA waiver for BEAD Program

Split Ratio 60/40
Splitter, quantity 4

Tray Orientation Left orientation

Page 1 of 2

NG4-VMKLF4J

Dimensions

 Height
 13.21 mm | 0.52 in

 Width
 159.77 mm | 6.29 in

 Depth
 130.3 mm | 5.13 in

Packaging and Weights

Packaging quantity

