NGFB-TB4MRDK



Next Generation Frame (NGF) Fiber Termination Block, 144 LC/UPC, singlemode, right oriented, downward cable exit, black

Product Classification

Regional Availability EMEA | Latin America | North America

Product Type Fiber patch block

Product Series NGFB

General Specifications

Functionality Patching

Application Used in NGF-style frames only

Body Style Right orientation

ColorBlackColor, frontBlack

Door Type, front Compression latch | Hinged

Growth ConfigurationFully loadedInterface, frontLC/UPCRack TypeNGFShelf MovementFixedTotal Ports, quantity144

Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

COMMSC PE®

NGFB-TB4MRDK

Environmental Specifications

 $\textbf{Operating Temperature} \qquad \quad -5~^{\circ}\text{C to } +50~^{\circ}\text{C (+23~^{\circ}\text{F to } +122~^{\circ}\text{F})}$

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 80%, non-condensing

Qualification Standards Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

