

QUFB-192FMPOSMHR

Q3000 Fiber Termination Blade (Module), 192 ports, MPO to MPO, Singlemode

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber modules in blade |
| Product Series | Q3000 |

General Specifications

| | |
|-------------------------------------|-------------------------------|
| Functionality | Breakout |
| Application | For use with Q3000 panels |
| Body Style | Duplex Straight orientation |
| Color, front | Black |
| Color, housing | Black |
| Color, rear | Black |
| Interface, front | MPO |
| Interface Feature, front | Standard |
| Interface, rear | MPO |
| Interface Feature, rear | Standard |
| Total Ports, quantity, front | 192 |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
| Fiber Type | OS2 |

Packaging and Weights

| | |
|---------------------------|--------------|
| Packaging quantity | 1 |
| Packaging Type | Bag Carton |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|-----------------------------------|
| CHINA-ROHS | Below maximum concentration value |

QUFB-192FMPOSMHR

| | |
|------------|--|
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |

