



## Highband® 12-Way Rack Kit, 4 RU

### Product Classification

<b>Regional Availability</b>	Australia/New Zealand
<b>Product Type</b>	Module patch panel
<b>Product Brand</b>	Highband®
<b>Product Series</b>	Highband

### General Specifications

<b>ANSI/TIA Category</b>	6
<b>Color</b>	Silver
<b>Growth Configuration</b>	Fully loaded
<b>Interface, front</b>	LSA-PLUS module
<b>Modules, quantity</b>	12
<b>Panel Mounting</b>	Recessed
<b>Panel Style</b>	Straight
<b>Rack Type</b>	EIA 19 in
<b>Rack Units</b>	4
<b>Transmission Standards</b>	ANSI/TIA-568-C.2   ISO/IEC 11801 Class E

### Dimensions

<b>Height</b>	177.8 mm   7 in
<b>Width</b>	482.6 mm   19 in

### Material Specifications

<b>Material Type</b>	High-impact, flame retardant, thermoplastic   Steel
----------------------	---

### Environmental Specifications

<b>Flammability Rating</b>	UL 94 V-0
----------------------------	-----------

# 64501178-01 | 6450 1 178-01

---

## Packaging and Weights

<b>Included</b>	Cable management bar
<b>Packaging quantity</b>	1
<b>Packaging Type</b>	Bag   Box

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

