# 760206979 | 1100A-U-GS6-KIT-2U



### 1100 ANGLED GS6 PANEL KIT - 2U

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin

America | North America

**Portfolio** SYSTIMAX®

Product Type RJ45 patch panel

General Specifications

ANSI/TIA Category 6A

Cable Type Unshielded

**Color** Black

Modules, quantity 8

Panel Style Angled

Rack Type EIA 19 in

Rack Units 2

Total Ports, quantity 48

**Dimensions** 

 Height
 88.9 mm | 3.5 in

 Width
 482.6 mm | 19 in

**Depth** 210.82 mm | 8.3 in

**Electrical Specifications** 

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Material Specifications

Material Type Powder-coated steel

Mechanical Specifications

**COMMSCOPE®** 

# 760206979 | 1100A-U-GS6-KIT-2U

#### Plug Insertion Life, test plug

IEC 60603-7 compliant plug

## **Environmental Specifications**

Operating Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  ( $-40 \,^{\circ}\text{F}$  to  $+158 \,^{\circ}\text{F}$ )

**Relative Humidity** Up to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 1

# Regulatory Compliance/Certifications

## Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

