760239071 | UDS-6U-WH-LA-A



Product Classification

UDS 6RU splice panel, 432 duplex LC/APC ports, Method A

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	UDS
General Specifications	
Application	Preloaded with 36 UDS modules
Color	White
Intelligence Type	Not iPatch® ready
Interface, front	LC/APC
Pigtail Assembly Type	12-fiber, ribbon
Pigtails Included, quantity	72
Rack Type	EIA 19 in
Rack Units	6
Shelf Movement	Fixed
Splice Trays Included, quantity	6
Total Ports, quantity	432
Dimensions	
Height	266.7 mm 10.5 in
Width	444.5 mm 17.5 in
Depth	609.6 mm 24 in
Optical Specifications	
Insertion Loss, maximum	0.4 dB

Page 1 of 2

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 24, 2025



760239071 | UDS-6U-WH-LA-A

Environmental Specifications

Safety Standard CUL US 1863

Packaging and Weights

Packaging quantity	1
Weight, net	20.412 kg 45 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: February 24, 2025

