

FD3-AE288J00JABP4



FDH 3000 Small Fiber Distribution Cabinet, 288F, SC/APC, no splitters, dielectric loose tube, 100 ft, 48F

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	3
Distribution Ports, quantity	288
Fibers per Distribution Cable, quantity	72
Fibers per Feeder Cable, quantity	48
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	12

Dimensions

Height	914.4 mm 36 in
Width	685.8 mm 27 in
Depth	457.2 mm 18 in
Cable Length	30.48 m 100 ft
Enclosure Size	Small

Material Specifications

Finish	Powder coated
Material Type	Aluminum

FD3-AE288J00JABP4

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

