FD3-AE288J2AGBBP1B



FDH 3000 Small Fiber Distribution Cabinet, 288F, SC/APC, 2 splitters, 1x32, single armor loose tube, 100 ft, 12F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeArmored - Single Loose Tube

Color Putty white

Distribution Cables, quantity 2

Distribution Ports, quantity 288

Fibers per Distribution Cable, quantity 144

Fibers per Feeder Cable, quantity 12

Interface, Input SC

Interface Feature, Input APC

Mounting Pole

Split Ratio Symmetrical

Splitter Slots, quantity 24

Splitter Type 1 x 32

Splitter, quantity 2

Dimensions

 Height
 914 mm | 35.984 in

 Width
 686 mm | 27.008 in

 Depth
 457 mm | 17.992 in

Cable Length 30.48 m | 100 ft

Enclosure Size Small



FD3-AE288J2AGBBP1B

Material Specifications

Finish Powder coated

Material Type Aluminum

Environmental Specifications

Environmental Space Aerial

Qualification StandardsTelcordia GR-3125-CORE

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

