

760237219 | CM12-4X6-SM-ULL



G2 ULL 4x6 Singlemode Conversion Module, (4) MPO-12 unpinned ports rear, (6) MPO-8 pinned front

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	SYSTEMAX ULL

General Specifications

Functionality	Breakout
Adapters, quantity, front	6
Adapters, quantity, rear	4
Color, front	Blue
Color, rear	Blue
Data Module Type	Fiber Conversion Module
Interface, front	MPO
Interface Feature, front	Reduced footprint
Interface, rear	MPO
Interface Feature, rear	Key up Unpinned
Polarity	Method B Enhanced (ULL)
Shuttered	No
Total Fibers, quantity	48
Total Ports, quantity, front	6

Dimensions

Height	26.42 mm 1.04 in
Width	96.52 mm 3.8 in

760237219 | CM12-4X6-SM-ULL

Depth 117.35 mm | 4.62 in

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.657.A2

Insertion Loss, maximum 0.7 dB

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant

Compliant

