

# 760237224 | CM24-2X6-LS-ULL



G2 ULL 2x6 Multimode OM4 Conversion Module, (2) MPO-24 unpinned ports rear, (6) MPO-8 pinned front

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber module
<b>Product Brand</b>	SYSTEMAX ULL

## General Specifications

<b>Functionality</b>	Breakout
<b>Adapters, quantity, front</b>	6
<b>Adapters, quantity, rear</b>	2
<b>Color, front</b>	Aqua
<b>Color, rear</b>	Aqua
<b>Data Module Type</b>	Fiber Conversion Module
<b>Interface, front</b>	MPO
<b>Interface Feature, front</b>	Standard
<b>Interface, rear</b>	MPO
<b>Interface Feature, rear</b>	Key up   Unpinned
<b>Polarity</b>	Method B Enhanced (ULL)
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	48
<b>Total Ports, quantity, front</b>	6

## Dimensions

<b>Height</b>	26.42 mm   1.04 in
<b>Width</b>	96.52 mm   3.8 in

# 760237224 | CM24-2X6-LS-ULL

---

**Depth** 117.35 mm | 4.62 in

## Optical Specifications

**Fiber Mode** Multimode  
**Fiber Type** OM4, LazrSPEED® 550  
**Insertion Loss, maximum** 0.4 dB

## Environmental Specifications

**Safety Standard** cUL US 1863

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

